



AR-261-13-03 (17.5")
 used with AR-431-11-03 (17.5 spring kit)

Instructions for use-

- 1- print PDF at "actual scale" 100% on A4 landscape
- 2- pattern is easier to use if glued to thin cardboard
- 3- use scissors to cut out pattern
- 4- hold pattern inside wheel to check compatibility
- 5- Check clearance of valve (optional dashed cutout) if invisivalves are not to be used
- 6- order best fitting foam heads with stated part number (eg AR-20X-12-03)

Note- this pattern can be up to 5mm out as foam heads and polishing fleece is designed to mould to different profiles

DESCRIPTION	SHEET 1-1
-------------	-----------

	DATE	PROJECT	Aussie Rimshine
--	------	---------	-----------------