



AR-271-13-03 (22.5x14x2" offset SS)

Instructions for use-

- 1- print PDF at "actual scale" 100% on A4 landscape
- 2- pattern is easier to use if glued to thin cardboard
- 3- use scissors to cut out pattern
- 4- hold pattern inside wheel to check compatibility
- 5- Check clearance of valve (optional dashed cutout) if invisivalves are not to be used
- 6- order best fitting foam heads with stated part number (eg AR-20X-12-03)

Note- this pattern can be up to 5mm out as foam heads and polishing fleece is designed to mould to different profiles

		DATE	PROJECT	DESCRIPTION	SHEET 1-1
				Aussie Rimshine	